

Cosmetics & Pharmaceuticals

Designed for transferring sensitive products and quick and easy hand cleaning as well as Cleaning In Place (CIP)

Advantages:

- Gentle on shear-sensitive products
- Seal-less design
- Line stripping capabilities
- Self priming
- Strong suction
- Small size / easy integration
- Flow rate not affected by viscosity or pressure variation
- Manual Cleaning (quick and easy dismantling)
- Cleaning In Place (CIP) accepted







Where Innovation Flows



S Series Pump Mouvex Eccentric Disc Technology

Performance Data

Pump	Maximum Flow Rate		Maximum Speed	Maximum Output Pressure		Maximum Temperature	
	L/hr	gpm	rpm	bar	psi	°C	°F
S2	1,500	6.61	900	6	87	80°	176°
S4C	4,000	17.6	750	6	87	80°	176°
S6C	12,000	52.8	500	6	87	80°	176°
S6C-HP	6,000	26.4	500	10	145	80°	176°

*SIP 248°F (20 minutes). please contact Mouvex for any other specific characteristics.

Pump body Low liquid volume Polished exterior **Blind nuts** • Wetted surface Ra 0.8 • Multi-directional inlet Outlet Quick dismounting Piston nut Removable Inlet **Couple Cylinder / Piston** without tools **Elastomer bellow** Removable without tools Long lasting (FKM) **Front Cover** Stainless steel 316 L / CY5SnBiM Isolate transmission · Polished exterior · Ability to dry run mechanical parts Multi-directional outlet • Ensure pump shaft sealing Low liquid volume

S4C ON MOBILE UNIT

S4C WITH FLEXIBLE HOSE



Products: Facial cream Gel shampoo

> Toothpaste Ointment Syrup

Body lotions and cleansers

S4C FOR CONDITIONING

Mouvex reserves the right to modify the information and illustrations contained in this document without prior notice. This is non-contractual document 03/2016 Authorized PSG[®] Partner:

S4C FOR TRANSFERRING

ZI la Plaine des Isles • 2 rue des Caillottes F-89000 AUXERRE - FRANCE Tel: + 33.3.86.49.86.30 • Fax: + 33.3.86.46.42.10 contact@mouvex.com mouvex.com

© 2016 MOUVEX